

Moyno Progressing Cavity Pump 331 Series

Mfg: Moyno

Model: 33104

Stock No. OIP159.

Serial No.

Moyno Progressing Cavity Pump. Model: 33104. Capacity: ½ gpm. Materials of Construction: 316 stainless steel housing and rotor, NBR (nitrile) stator. Mechanical seal: carbon ceramic. Baldor Industrial Motor, 3/4 hp, 1750 rpm, 90A/100/50 F V, 7.8/.6/1.2 amps, direct current. Drive, ratio: 4, 437 rpm out (final). Inlets/outlets: (2) 1 in. dia. FNPT fittings. Overall dimensions: 3 ft. L x 1 ft. W x 1 ft. 3 in. H.



