

1997 Hurst Vertical Tubeless Boiler 15 hp


Mfg: Hurst

Model: Cyclone(4VT-G-15-150)

Stock No. 97a.PFG02

Serial No. V55-150-364

1997 Hurst Vertical Tubeless Boiler- 15 hp. Model: Cyclone (4VT-G-15-150). S/N V55-150-364. Nat'l Board Number: 4536. Steam: 150 lb. BTU/hr input (min/max): 300,000/630,000 Btu/hr. MAWP: 150 psi. Heating surface: 55 sq.ft. Capacity: 518 lb/hour steam at 212 °F. Honeywell burner control. Power flame burner: Model: JR15A-10U. S/N 119727101. Natural gas: 300 MBH to 630 MBH. Control: 115 V, 1/4 hp. Gas manifold pressure (in WC): 2.86. Water capacity at NWL: 55 gallons; water capacity flooded: 69 gallons. Overall dimensions: 102 in. L x 60 in. W x 85 in. H.





PowerFlame Burner				
MODEL NO. JR15A-100				
SERIAL NO.		INVOICE NO.		
115727101		165803		
TYPE	MIN.	MAX.		
NAT GAS	300	MBH	630	MBH
		GPH		GPH
CONTROL VOLTS		115/10	AMPS	
MOTOR VOLTS		115/10	AMPS	9.3
		MOTOR HORSEPOWER		1/4
INTEGRAL CONTROL GROUP - GAS		6		
INTEGRAL CONTROL GROUP - OIL				
GAS MANIFOLD PRESS (IN. WC)		2.86		
PowerFlame Incorporated®				
PARSONS, KS P/N 01200				

