

2002 Winsmith Agitator Drive

Mfg: Winsmith



Model: 930CDSF

Stock No. PFGL173.7

Serial No.

2002 Winsmith Agitator Drive. Model: 930CDSF. P/N: 930CSFS096X0BT. Ratio: 7.5. Maximum input rpm: 1750. Output rpm: 234.6. Output torque: 11.48 in.-lbs. Shaft diameter: 2 in. Baldor Industrial Motor, 5 hp, 1760 rpm, 230/460 V, 6.8/3.4 amps, 60 Hz, 3 phase. Overall dimensions: 3 ft. 6 in. L x 1 ft. 8 in. W x 2 ft. H.





DRIVE MOTOR
SUPER-EFFICIENT INDUSTRIAL MOTOR
DALTON ELECTRIC CO. FORT SMITH

CAT. NO.	109N037071		
SPEC.	37H312Y15081		
FRAME	2037C	H.P.	5
VOLTS	230/480		
MAG. CUR.	6.0/3.4	13.4/8	
R.P.M.	1750	R.P.M. MAX	800
F. FZ.	50	PH	3 CLASS
SELT	1-00	DES	B SLHZ
NEMA NOM. EFF.	88.5	WK	734
CONTR.	V	PH	HZ
A.C. 370-CONT			
8201			
20110012-665			

