

Stainless Steel Cone Bottom and Closed Top Mix Tank- 100 Gallon

Mfg:

Model:

Stock No. RBPB133.2

Serial No.

Stainless Steel Cone Bottom and Closed Top Mix Tank- 100 Gallon. Inside dimensions (straight wall): 32 in. D x 30 in. H. 30 in. L x 6 in. W site glass on side. Baldor Industrial Motor, 1/3 hp, 208- 300/460 V, 1725 rpm, 1.8-1.6/0.8 amps, 60 Hz, 3 phase. Boston Gear Speed Reducer, 0.5 input hp (max), 20:1 ratio, 86.25 rpm (final), 342 ft/lbs of torque. Inlets: 1-1/2 in. port (top). Outlets: 1-1/2 in. port, 2 in. port, (1) 3-1/2 in. threaded fittings. Overall dimensions: 41 in. L x 39 in. W x 72 in. H.





