

FES 385 / Mycom 250S Rotary Screw Compressor Package Less Motor

Mfg: FES / Mycom

Model: 385 / 250S

Stock No: RCJF1522.12a

Serial No: 255-2155

FES 385 / Mycom 250S Rotary Screw Compressor Package Less Motor. Model: FES 385 / 250S. S/N: 2552155. Refrigerant last used with: R-717 (Ammonia). Displacement: 1,110 cfm. Oil separator: FES S/N: 82234. Natl. Bd. 1623. MAWP: 250 PSI at 300°F. Minimum allowable working temp: -20°F. Shell thickness: .375 in. Head thickness: .375 in. Radius: elliptical ends. Viking pump, model: AV477-AL. S/N: 1988480. Motor: Westinghouse motor: 7.5 hp, 1155 rpm, 230/460V, 22.4/11.2 amps, 60 Hz, 3 phase. Inlets/Outlets: (1) 5 in. dia. port. (1) 4 in. dia. port. (1) 1 ¼ in. dia. port. (2) 1 in. dia. port. (1) ¾ in. dia. port. Control panel model: Retrofit. S/N: 92295101. Overall dimensions: 13 ft. 5 in. L x 4 ft. W x 10 ft. 7 in. H. Compressor runtime: 69635.





