

# FES 315 / Howden WRV 204/1.93 Rotary Screw Compressor Package

Mfg: FES / Howden

Model: 315 / WRV 204/1.93

Stock No: RCJF1524.12a

Serial No: WRV204-19336-081

FES 315 / Howden 204/1.93 Rotary Screw Compressor Package. Model: 315. S/N: WRV204-19336-081. Control Panel: Model: FES315E. S/N: 88-0219-0301. Refrigerant: R-717. Fixed Vi setting: 3.6. Displaces 488 CFM at 1800 rpm. Leak test pressure: 313. Hydrostatic test pressure: 470. Oil Separator: FES, S/N: 88261. Nat'l Bd: 3643. MAWP: 250 psi @ 200°F. MDMT: -20°F @ 250 psi. Radius: elliptical ends. Pump: Viking Pump: Model: AV428AL. S/N: 5019514. Motor: 7.5 hp, 1175 rpm, 230/460 V, 20.4/10.2 amps, 60 Hz, 3 phase. Inlets/Outlets: (2) 1 in. dia. port. (1) 2 in. dia. port. Overall dimensions: 10 ft. 10 in. L x 4 ft. 3 in. W x 6 ft. 5 in H. Compressor runtime: 8291 hrs.



