

1996 Netzsch Incorporated Nemo® Stainless Steel Progressive Cavity Pump

Mfg: Nemo®

Model: 2NBS70A

Stock No: RCJF231.2

Serial No:

1996 Netzsch Incorporated Nemo® Stainless Steel Progressive Cavity Pump. Model: 2NBS 70A. Job no. 5292. Flow rate for new pump is 275 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum PSI: 180. Reliance Electric motor Industrial Co. motor: model no: P25G3311N. ID no: 33GP25331101G7WY, 15 HP, 1765 rpm, 18 amps, 460V, 60 Hz, 3 phase.(ACN288).





