

## Stainless Steel Bottom Jacketed Tank-500 Gallon

Mfg:

Model:

Stock No. RCPK506.11a

Serial No.:

Stainless Steel Bottom Jacketed Tank-500 Gallon. 304 Stainless steel. Rated for low pressure applications like hot/cold water. Tank features a dome top, flat bottom, and a top mounted heavy agitator. Reliance Electric motor, 5 hp, 1725 rpm, 460 V, 6.8 amps, 60 Hz, 3 phase. Jacket inlet/outlet: 1-1/2 in. threaded (female), 2-1/2 in. threaded (male). Tank outlets: 2-1/2 in. S-line. Manway: 23 in. diameter, Inlet: 2 in. S-line, 2 in. threaded (male), 1-1/2 in. S-line, (3) 2-1/2 in. S-line, side mounted: 2-1/2 in. threaded (male). Overall dimensions: 70 in. diameter x 96 in. H.





