

## Waukesha 220 Positive Displacement Pump

**Mfg: Waukesha Cherry-Burrell**

**Model: 220**

**Stock No.: RCSC537.75**

**Serial No.: 300181-02**

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220. S/N: 300181-02. 3A Sanitary. Universal I series. Maximum pressure: 200 PSI. Flow rate for new pump is 310 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Estimated flow rate with this gear drive is 63 GPM. SEW-Eurodrive gear drive ratio: 14.05 (final RPM 122). Baldor Motor: 5 HP, 460V, 6.6 amps, 1725 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions: 4 ft. 7 in. L x 1 ft. 6 in. W x 1 ft. 10 in. H. (ACN208-265)







