

Waukesha 220 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 220

Stock No.: RCSC592.75

Serial No.: 130080CR 06

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220. S/N: 130080CR 06. Previously remanufactured. 3A Sanitary. Universal I series. Flow rate for new pump is 310 gpm with required horsepower and RPM. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Maximum pressure: 200 PSI. Estimated flow rate with this gear drive is 93 GPM. SEW-Eurodrive gear drive ratio: 9.64 (final RPM 179). Baldor Motor: 5 HP, 460V, 6.6 amps, 1725 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions 4 ft. 8 in. L x 1 ft. 8 in. W x 1 ft. 11 in. H. (ACN208-265)







