

2000 AGC ProFlow Plate Heat Exchanger

Mfg: AGC

Model: A65

Stock No: RCSC888.50

Serial No: 00209

AGC ProFlow Plate Heat Exchanger. Model: A65. S/N: 00209. Max pressure: 150 PSI. Year: 2000. Stainless steel plates and tie bars. Number of plates: 186. Plates measure roughly 24 in. wide x 50 in. high. Approximate surface area: 1,550 square feet. Ports: 8.25 in. ID. Overall dimensions: 4 ft. 6 in. L x 36 in. W x 67 in. H.

