

Cherry Burrell Stellar Series Superhomo Homogenizer

Mfg: Cherry Burrell

Model: SS-5000-TGR

Stock No. RFBM344.42a

Serial No. 280959

Cherry Burrell Stellar Series Superhomo Homogenizer. Model: SS-5000-TGR. 2-Stage manual valve assembly. 2-5/8 in. dia. plungers. Maximum operating pressure: 2000 psi. Tapered seat poppet valve cylinders. Maximum capacity: 3000 gph. S/N: 280959.

Power frame exterior is a gleaming stainless steel. Its adjustable tow-stage Homogenizing valves with replaceable caps absorb 98% of valve wear and increase homogenizing efficiency. Reliance Electric Motor, 125 hp, 1750 rpm, 667 rpm (final), 230 V, 294 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. I-line fitting. Outlets: (1) 1-1/2 in. dia. I-line fitting. Overall dimensions: 64 in. L x 46-1/2 in. W x 62 in. H.



