

Ingersoll-Rand Centrifugal Pump

Mfg: Ingersoll-Rand

Model: A 0462-5129

Stock No: RGMP281D

Serial No: 3RVS-7-1/2

Ingersoll-Rand Centrifugal Pump. Model: A 0462-5129. Type: 3RVS-7-1/2. Flow rate for new pump is 360 gpm with required horsepower and pressure. Discuss with sales person your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 4.875 in. Hydrostatic test pressure: 100 psi. Seal: 10043. General Electric motor, 7-1/2hp, 3520/2930 rpm, 208-220/440 V, 19.6/9.8; 20/10 amps, 60/50 Hz, 3 phase. Inlet: (1) 4-1/2 in. dia. port. Outlet: (1) 2-1/2 in. dia. port. Overall dimensions: 2 ft. 4 in. L x 1 ft. 1 in. W x 1 ft. 1 in. H.



