

Bell & Gossett Centrifugal Pump

Mfg: Bell & Gossett

Model: 11/4BC-75/8-BF

Stock No: RGMP404

Serial No: 1203461

Bell & Gossett Centrifugal Pump. Model: 11/4BC-75/8-BF. S/N: 1203461. Impeller diameter: 7-3/4 in. Flow rate for new pump is 35 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum working pressure: 175 psi. Century electric motor, 1-1/2 hp, 1745 rpm, 230/460 V, 4.4/2.2 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. dia. FNPT fitting. Outlet: (1) 1-1/2 in. dia. FNPT fitting. Overall dimensions: 2 ft. 7 in. L x 1 ft. 3 in. W x 2 ft. 3 in. H.





