

LANDA® CLEANING SYSTEMS

Since 1969

Industrial Pressure Washers and Parts Washers
...Built Right to Do the Job Right

NOW WITH
**TWO
WIRELESS
REMOTE
OPTIONS!**

SEA

Stationary, Electric-Powered,
Cold Water Pressure Washer

- Up to 4.2 GPM, 3000 PSI
- LanCom Wireless Remote Control Option
- Stainless Steel Cabinet
- Time-Delay Shutdown
- Accepts Hot Water Up to 175°F

■ **Industrial-grade Motor** is connected to the rugged, tri-plunger, oil-bath **LANDA High-Pressure Pump** (with 7-year warranty) by dual, heat-dissipating V-cogged belts. **Pulleys** are made of cast iron and can be easily adjusted by turning two bolts.

■ Four quick-couple **Nozzles** are made of hardened stainless steel and color-coded for easy selection of spray pattern: 0°, 15°, 25°, 40°.

■ Heavy-duty **Stainless Steel Cabinet** rides on four **Rubber Feet** for absorption of vibration.

■ Add portability to the SEA with optional ► stainless steel **Wheel Kit** (#4-03177), including detergent jug holder. Optional **Hose Reel** (#4-02755030) provides tangle-free handling of up to 100 feet of high-pressure hose.



■ **Inlet Filter** strainer protects pump from debris.



■ Insulated, fatigue-free, spring-loaded, 5000 psi **Trigger Gun** with stainless steel, dual-lance **Variable Pressure Wand** make for easy cleaning and adjusting the pressure while washing.

■ 50 ft. of double steel-wire braid **High Pressure Hose** rated for up to 6000 PSI and with 24-inch **Hose Guard** for burst protection and swivel crimp fitting for tangle-free handling of hose and trigger gun

■ **Time-Delay Shutdown** automatically turns off unit, if not in use for a set time, for protection against unattended operation.

■ 36 ft. of high-grade **Electrical Cord** with **Ground Fault Circuit Interrupter** (on single-phase models) for operator safety.

■ Many **Safety Features**, including a thermal pump protector to prevent the build up of excessive pressures or heat.

■ With the switch in the 'ON' position, the optional **Auto Start** function allows the unit to be turned on with the pull of the trigger for convenient remote operation. (This option replaces Time Delay Shutdown.)

■ Helpful **Tri-Lingual Labels** with operating instructions in English, Spanish and French for added liability protection and operator convenience.

■ Optional rust-free **Float Tank** with stainless steel inlet filter and back-flow protection (cannot be ordered with wheel kit option).

■ Easy-to-attach **Detergent Injector** for easy application of soap



■ Control the SEA from up to 300 ft. away with the **LanCom Wireless Remote** option. Saves time with the ability to control the SEA while on a ladder or scaffolding. Two versions available for controlling the pump and 1-Step or 2-Step detergent application.

www.landa.com

LANDA® CLEANING SYSTEMS

Since 1969

Industrial Pressure Washers and Parts Washers
...Built Right to Do the Job Right

SEA

Stationary, Electric-Powered,
Cold Water Pressure Washer

- Up to 4.2 GPM, 3000 PSI
- LanCom Wireless Remote Control Option
- Stainless Steel Cabinet
- Time-Delay Shutdown
- Accepts Hot Water Up to 175°F

LanCom
Wireless
Remote
Control
Option



**TWO
WIRELESS
REMOTE
OPTIONS!**

Remotely controls pump and
injection of detergent from
one or two sources

WHY CHOOSE LANDA'S SEA

The SEA is the absolute top-of-the-line stationary, cold water pressure washer on the market today. The 11 models feature *LANDA* belt-drive pumps and are ideal for indoor cleaning applications, from food processing to warehouse cleaning. *Now available with optional LanCom wireless remote.*

QUALITY: Only the highest quality components are found in the SEA, including the *LANDA* tri-plunger high-pressure pump with 7-year warranty, stainless steel cabinet riding on four vibration-absorbing feet and stainless steel variable pressure wand for maximum cleaning flexibility. Also, the SEA is assembled in a factory certified to the internationally recognized ISO-9001 quality standards.

SAFETY: The SEA also is certified to the rigid UL-1776 safety standards making it very safe to operate thanks to its magnetic contactor switch with thermal overload protection, time-delay shutdown, 24-inch hose guard for burst protection, Ground Fault Circuit Interrupter on all single-phase models, and tri-lingual operating instructions.

SEA Specifications

Part No.	GPM	PSI	Motor HP	Electrical	Amps	Cord Length	Pump RPM	L x W x H	SHIP WT.
SEA3-11024D	2.8	1000	2	120V 1 ph	20	36 Feet w/GFCI	1540	26" x 20" x 16"	205 lbs.
SEA4-20024A	4.2	2000	6.2	230V 1 ph	28	36 Feet w/GFCI	935	26" x 20" x 16"	280 lbs.
SEA4-20024B	4.2	2000	6.2	230V 3 ph	16	10 Feet	935	26" x 20" x 16"	220 lbs.
SEA4-20024C	4.2	2000	6.2	460V 3 ph	8.2	10 Feet	935	26" x 20" x 16"	220 lbs.
SEA4-20024F	3.5	2000	5	575V 3 ph	6.5	10 Feet	935	26" x 20" x 16"	220 lbs.
SEA4-20024G	4.2	2000	6.2	208V 1 ph	30	36 Feet w/GFCI	900	26" x 20" x 16"	220 lbs.
SEA4-20024H	4.2	2000	6.2	208V 3 ph	18.5	10 Feet	900	26" x 20" x 16"	220 lbs.
SEA4-30024B	3.5	3000	7.5	230V 3 ph	21.5	10 Feet	800	26" x 20" x 16"	235 lbs.
SEA4-30024C	3.5	3000	7.5	460V 3 ph	10.5	10 Feet	800	26" x 20" x 16"	235 lbs.
SEA4-30024F	3.5	3000	7.5	575V 3 ph	9	10 Feet	735	26" x 20" x 16"	235 lbs.
SEA4-30024H	3.5	3000	7.5	208V 3 ph	25	10 Feet	750	26" x 20" x 16"	220 lbs.

Note: We are constantly improving and updating our products. Consequently, pictures, features, and specifications in this brochure may differ slightly from current models. Flow rates and pressure ratings may vary due to variances allowed by manufacturers of our machine components. We attempt to keep our machine performance within ±5% of listed specifications.

LANDA®
CLEANING SYSTEMS

Distributed by:

OPTIONS:

Part No.	Description	
89301630	LanCom Wireless Remote with one detergent*	* LanCom Remote Option not compatible with Auto Start/Stop or Float Tank Options
89301770	LanCom Wireless Remote with two detergents*	
30-487	Automatic Start/Stop (replaces Time-Delay)	
30-640	Wall Mount Bracket Assembly, Stainless Steel	
4-03177	SEA Stainless Steel Wheel Kit (not compatible with Float Tank Option)	
30-332	Float Tank Option with Inlet Detergent Injection	
30-5020	E-Zee Reel Hose Reel, 100 ft. & mounting kit (mounts to wall mount bracket or wheel kit)	
30-415	Remote Switch Option (hardwire)	

www.landa.com