

1984 E.L. Nickell Vertical Ammonia Receiver

Mfg: E.L. Nickell

Model:

Stock No: RPCA1360.4

Serial No:

1984 E.L. Nickell Vertical Ammonia Receiver. Nat. Bd. no: 33169. ELNCO: 33400. 150 Psi Max. W.P. 650° F Max. Temp. -20° F Min. Temp. (2) 2-1/2 in. inlet/outlet with Henry valves. (1) 8 in. flanged Wolf Linde shut off valve. (1) 8 in. flanged side inlet/outlet. (2) 1-1/2 in. inlet/outlet. (2) 150 psi set safety relief valves. Tank dimensions: 6 ft. dia. x 10 ft. H dome to dome. Tank Straight wall length: 6 ft. 8 in. Overall dimensions: 7 ft. 8 in. W x 6 ft. L x 13 ft. 4 in. H.



