

## Hansen Technologies Auto-Purger




**Mfg: Hansen Technologies**


**Model: APC**

**Stock No.: RPCN076.7a**

**Serial No.: M2039**

Hansen Technologies Auto-Purger. Model: APC. S/N: M2039. Single point purger. Refrigerant: R-717 (ammonia). Set pressure: 400 psig. Power supply: 120 V, 8.0 amps, 60 Hz. Evaporator Chamber. Water Bubbler. (2) Henry Technologies Relief Valves. Hansen Technologies Fluid Float Switch. (5) Hansen Technologies Solenoid Valves. Hansen Technologies Liquid Drainer. Hoffman Control Panel. The AUTO-PURGER is an automatic, electronically-controlled noncondensable gas (air) refrigerant purger for reducing condensing pressure. Inlets: (1) 1/2 in. dia. low pressure pumped-liquid line, (1) 1/2 in. dia. foul gas line, (1) 1/2 in. dia. water bubbler fill line. Outlets: (1) 1 in. dia. bubbler drain port, (1) 1/2 in. dia. low pressure liquid drain port, (1) 3/4 in. dia. suction line. Overall dimensions: 3 ft. 1/2 in. L x 1 ft. 9 in. W x 4 ft. 9 in. H.





**AUTO-PURGER**

Model	APC
Voltage/Hertz	120/60
Amps	6.0
Serial Number	R2039

400 PSIG (27 bar) SWP

**HANSEN TECHNOLOGIES CORPORATION**  
Burr Ridge, IL 60521 USA

85

**Hoffman**

TO MAINTAIN THE ENVIRONMENTAL RATING OF THIS ENCLOSURE, INSTALL IN ANY OPENINGS ONLY LISTED OR RECOGNIZED CONDUIT HUBS OR CONTROL DEVICES WITH THE SAME ENVIRONMENTAL RATING AS THE ENCLOSURE, IN COMPLIANCE WITH THE INSTALLATION INSTRUCTIONS OF THE DEVICE.

CAT. NO. A-16N128

**UL** UNDERWRITERS LABORATORIES LISTED

CUTOUT BOX ISSUE NO. J-0492

ENCLOSURE TYPE 1

C.S.A. ENCLOSURE TYPE 1

TO MEET C.S.A. GROUNDING REQUIREMENTS, SEE DEGROUNDING KIT HOFFMAN CATALOG NUMBER H-0527

ELECTRIC BOX