

Bell & Gosset 3530 Series Centrifugal Pump

Mfg: Bell & Gosset

Model: 30-4T 1AM008 E49

Stock No.: RPCN163C

Serial No.:

Bell & Gosset Centrifugal Pump. Model: 30-4T 1AM008 E49. Series: 3530. Maximum working pressure: 125 psi. Impeller diameter: 7 in. Franklin Electrical Motor, 1-1/2 hp, 3450/2875 rpm, 208-230/460 V, 4.5-4.8/2.4 FLA, 60/50 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. FNPT. Outlets: (1) 1 in. dia. FNPT. Overall dimensions: 1 ft. 2-3/4 in. L x 8 in. W x 9-1/2 in. H.





Franklin Electric
800-467-14

MOD 1303007169	HZ 60/50	KVA
V 208-230/460	FR 56J	CODE M
HP 1 1/2	SF 1.3	ENC DP
RPM 3450/2875	MAX AMB 40	PH 3
FLA 4.5-4.8/2.4	TIME RATE COM	INS B
SFA 5.5-5.8/2.9	CAT	DATE CODE C94
CO7878BG		
V 380/415 HZ 50 A 2.5/2.7		

WARNING
ALWAYS DISCONNECT MOTOR FROM POWER SUPPLY BEFORE SERVICING.
MOTOR CONTAINS NO THERMAL PROTECTOR

LOW VOLTAGE

Franklin Electric
800-467-14

MOD 1303007169	HZ 60/50	VOLTS
V 208-230/460	FR 56J	ENC DP
HP 1 1/2	SF 1.3/1.0	PH 3
RPM 3450/2875	MAX AMB 40	INS B
FLA 4.5-4.8/2.4	TIME RATE COM	
SFA 5.5-5.8/2.9	CAT	DATE CODE C94
CO7878BG		
V 380/415 HZ 50 A 2.5/2.7		

WARNING
ALWAYS DISCONNECT MOTOR FROM POWER SUPPLY BEFORE SERVICING.
MOTOR CONTAINS NO THERMAL PROTECTOR
SEPARATE OVERCURRENT PROTECTION MUST BE PROVIDED TO PREVENT BURN OUT AND POSSIBLE FIRE HAZARD FROM OVERLOAD OR STALLED MOTOR.
GROUNDING
FATAL ELECTRICAL SHOCK MAY RESULT IF MOTOR FRAME AND ADJACENT METAL IS NOT GROUNDED IN COMPLIANCE WITH ELECTRICAL CODE.

LOW VOLTAGE

HIGH VOLTAGE

MADE IN USA

WARNING
ROTATING COMPONENTS
DANGER
PUMP OIL
MAY ESCAPE

ITT Bell & Gossett

SERIES 3530 MAX. W.P. 125 PSI.

MODEL 30-4T 1AM008 E49

Morton Grove, IL USA

ITT Bell & Gossett

SERIES 3530 MAX. W.P. 125 PSI.

MODEL 30-4T 1AM008 E49

Morton Grove, IL USA

ITT Bell & Gossett

SERIES 3530 MAX. W.P. 125 PSI.

MODEL 30-4T 1AM008 E49

Morton Grove, IL USA

ITT Bell & Gossett

3530 MAX. W.P. 125 PSI.

30-4T 1AM008 E49

Morton Grove, IL USA