

## Teel Centrifugal Water/Glycol Chiller Pumps

Mfg: Teel

Model: 3P604, 4RH63, 4XZ08

Stock No.: RPCN204B

Serial No.:

(2) Teel Centrifugal Pumps. Model: 3P604. Impeller diameter: 4-1/8 in. (2) Dayton Motors, 2 hp, 3485 rpm, 208-230/460 V, 6.0-2.5/2.9 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. FNPT port. Outlets: (1) 2 in. dia. FNPT port. Overall dimensions: 1 ft. 6 in. L x 9-1/2 in. W x 9-1/2 in. H.

(1) Teel Centrifugal Pump. Model: 4RH63. S/N: T0293. Impeller diameter: 4 in. Dayton Motor, 1-1/2 hp, 3450 rpm, 208-230/460 V, 5.0/2.5 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. FNPT port. Outlets: (1) 1-1/2 in. dia. FNPT port. Overall dimensions: 1 ft. 3-1/2 in. L x 7 in. W x 6-1/2 in. H.

(1) Teel Centrifugal Pump. Model: 4XZ08. Impeller diameter: 5-1/2 in. Franklin Motor, 2 hp, 3450/2875 rpm, 5.4/2.7 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. FNPT port. Outlets: (1) 1-1/2 in. dia. FNPT port. Overall dimensions: 1 ft. 3-1/2 in. L x 9 in. W x 9 in. H.







Dayton THREE PHASE MOTOR

MODEL	9NGB4	HP	2.0	PH	3
NEMA DESIGN	B	FRAME	145JM	RPM	2880
NS	60	SF	1.25	INSUL CLASS	F
MOTOR REF	6A0816K921E1110000				
DUTY	CONT	MAX AMB	40°C	MAX KVAR	
SHAFT END BRG	6207	OPP END BRG	3205	TYPE	TE
NEMA EFFICIENCY	80%	POWER FACTOR		ENCL	TE

MADE FOR DAYTON ELECTRIC MFG. CO. CHICAGO 60648 U.S.A.

**WARNING:** MOTOR MUST BE GROUNDED IN ACCORDANCE WITH LOCAL AND NATIONAL ELECTRICAL CODES TO PREVENT SERIOUS ELECTRICAL SHOCKS

Dayton Industrial Motor

MODEL NO	2NGB4	VOLTS	208-230/240
HP	2.0	RPM	2880
PH	3	FRAME	145JM
SF	1.25	HZ	60
ENCL	TE	MAX AMB	40°C
DUTY	CONT	POWER FACTOR	80%
MAX KVAR		SHAFT END BRG	6206
MOTOR REF	H00 H22500 F		

Manufactured for Dayton Electric Mfg. Co., Niles, IL 60714 U.S.A.

**SPECIAL FEATURES**  
50HZ HP 2.0 RPM 2880  
VOLTS 208/230/240 FIA 6-B/3-4

