

APV R57 Plate Heat Exchanger – 1044 Sq. Ft.

Mfg: APV Crepaco

Model: R57

Stock No: SAF162a.8

Serial No: 25590

APV Plate Heat Exchanger. Model: R57. S/N: 25590. Stainless steel plates: (167). Section 1: (37) plates, Section 2: (113) plates, Section 3: (17) plates. Overall plate dimensions: 1 ft. 4 ½ in. x 5 ft. 1-3/8 in. Heat transfer surface area measured from: 1 ft. 3 in. x 5 ft. as approximately 1044 sq. ft. Maximum temperature: 239°F. Maximum pressure: 200 psig. Fixed end ports: (3) 4 in. Movable end ports: (3) 4-1/2 in. Divider 1 ports: (2) 2-1/2 in., (1) 3 in. Divider 2 ports: (1) 2 in., (1) 2-1/2 in. Overall dimensions: 7 ft. 6 in. L x 2 ft. 1 in. W x 5 ft. 10 in. H.

