

## Meyer Vibrating Conveyor

Mfg: Meyer

Model:

Stock No. SBPP60.4

Serial No. 248

### Meyer vibrating conveyor.

- S/N 248, Unimount motor,
- ID A5 13/POIN274R048F,
- ¾ hp, frame 56C, 230/460 volts, 3 phase, 1,775 rpms, 60 Hz, F.L. amps 2.8 - 1.4, S.F. 3.2 - 1.6,
- Inside dimensions 13 in. W, 83 in. L, 4 in. D,
- Overall 101 in. L, 26in. W, 33 in. H.

