

## Tyson Pneumatic Filler with Mixer Hopper

Mfg: Tyson

Model:

Stock No. SELM106.14

Serial No.

Tyson Pneumatic Filler. Piston Diameter: 2-3/8 in. Stroke: 3-1/2 in. Valve Diameter: 1 in. Center between valves: 2-1/2 in. Max. Fill volume 10 oz .283 lt. Capacity: 30 BPM. Conveyor: 3-1/4 in. Bottle Dimensions: Minimum 2-1/2 in. Mixer/hopper 200 liters. Approx. 8 cu ft. Inside dimensions: 36 in. L x 17-1/2 in. W x 24-1/2 in. H. Overall dimensions: 90 in. L x 78 in. W x 71-1/2 in. EXR



