

3M Adjustable Case Sealer

Mfg: 3M

Model: 700a

Stock No: SFEC3801.3

Serial No: 12431

3M 3M-Matic™ Adjustable Case Sealer. Model no. 700a. Serial no. 12431. Capacity: 40 cases per minute. Handles cases 6 in. and up in length. Min/max case width: 6 in. to 1 ft. 8-1/2 in. Min/max case height: 4-3/4 in. to 2 ft. 1/2 in. (1) Bodine Electric Co. motor: Type no. 42X5BFCI-E2. 1/6 Hp, 115 rpm, 115 V, 1.9 A, 60 Hz, 1 Ph, 68 lb-in torque, 15:1 ratio. Features include: dual masts for stability and uniform height adjustments, 3M™ AccuGlide™ taping heads for low-impact application of tape 36 mm to 48 mm wide, and adjustable slide guides for quick changeover for different size case runs. Overall dimensions: 4 ft. 10-1/2 in. L. x 2 ft. 7 in. W. x 6 ft. 6 in. H.





