

Stainless Steel CIP Skid

Mfg:

Model:

Stock No. SFEP003.6a

Serial No.:

Stainless Steel CIP Skid. S.O: 2925. 180-Gallon stainless steel tank. 18-Gallon stainless steel vacuum tank. Control requirements: 480 V, 20 amps, 60 Hz, 3 phase. APV Recirculating Centrifugal Pump, Model: 16V2, S/N: 100268162. Sterling Electric Motor, 1-1/2 hp, 1750 rpm, 208-230/460 V, 4.84-4.38/2.19 amps, 60 Hz, 3 phase. Overall dimensions: 100 in. L x 33-1/2 in. x 78 in. H. Atlantic Fluidics Liquid Ring Vacuum Pump, Model: 12010. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 13.2-12/6 amps, 60 Hz, 3 phase. Pick Steam Injection Liquid Heater, Model: 6x7-3, S/N: 0502-05, liquid flow: 15 gpm, temperature rise: 90 °F, steam pressure: 100 psi, water pressure: 50 psi. (2) Tri-Clover Pneumatic Flow-Divert Valves, Model: 761TR-10M-20S-1-316L.



