

Chisholm Ryder Green Bean Cutter

Mfg: Chisholm Ryder

Model: BST542C

Stock No. SFEP1322A.a

Serial No.

Chisholm Ryder Bean Cutter. Model: PST542C. S/N: BST542C. Infeed hopper dimensions: 2 ft. L x 1 ft. 8 in. W. Drum dimensions: 2 ft. dia. x 6 ft. 11 in. L. Flight dimensions: 11-1/2 in. L x 11-1/2 in. W. Flight pitch: 2 in. (2) 6 ft. 11 in. W x 2 ft. 5 in. H access doors. Sterling Electric Motor, 3/4 hp, 1730 rpm, 208-230/460 V, 2.27-2.20/1.10 amps, 60 Hz, 3 phase. Speedtronics Gear Drive, 25 ratio, 69.2 rpm (final). Inlets: (1) 1 ft. 3 in. dia. infeed. Outlets: (1) 1 ft. 3 in. dia. discharge. Overall dimensions: 9 ft. 9-1/2 in. L x 2 ft. 10 in. W x 6 ft. 2 in. H.





