

## Sine SPS-35 Positive Displacement Pump

Mfg: Sine

Model:

Stock No. SFF447.15

Serial No. 13108SP-002

Sine SPS-35 Positive Displacement Pump. S/N: 13108SP-002. Capacity: 35 gpm. I.D: 208. Displacement per revolution: 0.25 gal/rev. Reliance Electric Motor, 10 hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Dodge APG Gear Reducer, 11.4 ratio, 153.94 rpm (final). Patented design assures powerful suction for high viscosity applications. Constant volumetric displacement creates a smooth and consistent flow. One rotor, one shaft, and one seal assembly equate to simple, economical maintenance. Capable of handling viscous, shear sensitive or aggregate liquids while providing powerful suction lift and a pulse-free laminar flow. Ideal for the following industries: bakery, dairy, confectionary, food processing, beverage, pharmaceutical, and cosmetic. Inlets/outlets: (2) 3 in. dia. S-line fittings. Overall dimensions: 52 in. L x 17 in. W x 17 in. H.



