

**APV Gaulin G132 Ball Valve Homogenizer – 2900 PSI**

**Mfg: APV Gaulin**

**Model: G132Q-3BX**

**Stock No: SFPC034.275**

**Serial No: 19982410097**

1998 APV Gaulin Homogenizer. Model: G132Q-3BX. Max capacity of 3846 GPH. Max Working Pressure: 2,900 PSIG. Pressure and flowrate can be modified/adjusted to suit your needs. Ball valves. 2-3/4 in. (70mm) plungers. Anderson controls. Marathon Electric motor: 125 HP, 1780 RPM, 460V, 146 A, 60 Hz, 3-phase. Lube pump motor: TEFC, 1/2 hp, 3 phase, 60 Hz, 230/460 volts, 1800 rpm. Hydraulic pump motor: TEFC, 1/3 hp, 3 phase, 60 Hz, 230/460 volts, 1800 rpm. Inlet/outlet: (2) 3 in. S-line. Inlet/outlet: (2) 3 in. tri-clamp. Approximate weight: 12,500 lbs. Overall dimensions: 6 ft. 2-1/2 in. L x 9 ft. 3 in. W x 4 ft. 10-1/2 in. H.(ACN2284-98).





























