

A&D Stainless Steel Housing with Mild Steel Screw Auger

Mfg: A&D

Model:

Stock No. SGML097.1

Serial No.

A&D Stainless Steel Housing with Mild Steel Screw Auger. SEW motor, 3 hp, 1700 rpm, 230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. SEW Eurodrive, 26.96 ratio, Out rpm: 65, torque: 2907. Screw: mild steel, 8-1/2 in. dia. x 100 in. L. Inlet: 10 in. L x 8-1/2 in. W. Outlet/discharge: 10 in. W x 10 in. H. Overall dimensions: 10 ft. 2 in. L x 35 in. W x 20 in. H.



