

Goulds Centrifugal Pump

Mfg: Goulds

Model: 3196

Stock No: SHCA1390.8a

Serial No: 707D143

Goulds Centrifugal Pump. Model: 3196. S/N: 707D143. Size: 1x1.50-6. Flow rate for new pump is 150 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 5.50 in. Maximum speed: 3600 rpm. Weg Motor, 7.5 hp, 3455 rpm, 575 V, 8 amps, 60 Hz, 3 phase. The 3196 pump is a horizontal overhung, open impeller, centrifugal pump that meets the requirements of ANSI B73.1. Inlets: (1) 1-1/2 in. dia. suction ANSI flat-faced flange. Outlets: (1) 1 in. dia. discharge ANSI flat-faced flange. Overall dimensions: 3 ft. 2-5/8 in. L x 1 ft. 2 in. W x 1 ft. 4 in. H.(ACN71).





