

APV R6 Series Positive Displacement Pump

Mfg: APV


Model: R6RIHD

Stock No: SIBI147E.10

Serial No: PP-1938-0499

APV R6 Series Positive Displacement Pump. Model: R6RIHD. S/N: PP-1938-0499. Flow rate for new pump is 240 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance Electric motor 10 hp, 1755 rpm, 230/460 volts, 25.4/12.7 amps, 60 Hz, 3 phase. Motor drive 5.0 ratio, 1750/350 rpm in/out, 3495 torque. Inlets: (1) 10 in. flange (12) mounting holes 7/8 in. dia. 3-5/8 in. adjacent 14-1/4 opposite. (2) 2 in. s-line. Outlet: (1) 3 in. s-line. Overall dimensions: 5 ft. L. x 1 ft. 10 in. W. x 2 ft. 3-1/4 in. H.(ACN170).





FRAME	TYPE	DESIGN	IDENTIFICATION NO.	MODEL NO.	
P213C	P	B	076P213864010	6 CE P21038640	
HP 40	VOLTS	230/460	Hz 60	PHASE 3	CODE G
IPW 1755	AMPS	25.4/12.7	S.F. 1.15	AMB 40°C	INSUL CLASS F
ENCL TEFD	DUTY CONT			WGTOR 157 LBS	
DRIVE SH 358C02/PP30A	BEARING 358C02/PP30A				
B1550 CERT STD 29 1/1/70					
RELIANCE ELECTRIC INDUSTRIAL CO. MADE IN U.S.A.					