

Timing Screw

Mfg:	Model:
Stock No. SLSP016.a	Serial No.:

Timing Screw. Shaft diameter: 2 in. Screw dimensions: 4-1/2 in. dia. x 4 ft. 1/4 in. L. Overall dimensions: 4-1/2 in. dia. x 4 ft. 3-1/2 in. L.

Timing Screw. Shaft diameter: 2 in. Screw dimensions: 4-1/2 in. dia. x 3 ft. 10-1/2 in. L. Overall dimensions: 4-1/2 in. dia. x 4 ft. 1/2 in. L.

Timing Screw. Shaft diameter: 2 in. Screw dimensions: 4-1/2 in. dia. x 4 ft. 2 in. L. Overall dimensions: 4-1/2 in. dia. x 4 ft. 3-1/2 in. L.

Timing Screw. Shaft diameter: 2 in. Screw dimensions: 4-1/2 in. dia. x 4 ft. 2 in. L. Overall dimensions: 4-1/2 in. dia. x 4 ft. 3-1/2 in. L.

Timing Screw. Shaft diameter: 2 in. Screw dimensions: 4-1/2 in. dia. x 3 ft. 11 in. L. Overall dimensions: 4-1/2 in. dia. x 3 ft. 11-1/4 in. L.

Timing Screw. Shaft diameter: 1-3/4 in. Screw dimensions: 4 in. dia. x 4 ft. L. Overall dimensions: 4 in. dia. x 4 ft. 2 in. L.

Timing Screw. Shaft diameter: 1-3/4 in. Screw dimensions: 4 in. dia. x 4 ft. 1/4 in. L. Overall dimensions: 4 in. dia. x 4 ft. 2 in. L.

Timing Screw. Shaft diameter: 1-3/4 in. Screw dimensions: 3-3/4 in. dia. x 2 ft. 6 in. L. Overall dimensions: 3-3/4 in. dia. x 2 ft. 11 in. L.

Center Guide. Overall dimensions: 2 ft. 1-3/4 in. L x 1 ft. 11-1/4 in. W x 7-1/4 in. H.

Infeed Star. Bottle width: 4-3/4 in. Shaft diameter: 1-1/2 in. Overall dimensions: 1 ft. 5-1/8 in. L x 1 ft. 5-1/8 in. W x 3-1/2 in. H.



