

## Waukesha Model 125 Positive Displacement Pump

Mfg: Waukesha

Model: 125

Stock No: SLTN001

Serial No: DO66314 SS

Waukesha Positive Displacement Pump. Model: 125. S/N: DO66314 SS. Flow rate for new pump is 140 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Waukesha pumps feature ease of cleaning and disassembly without the use of tools. Rotors, body, and all parts in contact with the product are designed and manufactured for acceptability by USDA and 3-A sanitary standards. Rotors and body are constructed of 316 stainless steel. Typical applications include: milk, vegetables, fruits, flavorings, bakeries and meats. Reliance Electric drive. Motor: 10 hp, 230/460 V, 25.4/12.7 amps, 1755 rpm, 215C frame, 3 phase, 60 Hz. Gear box ratio: 5. Final rpm: 350. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 4 ft. 3 in. L x 1 ft. 10 in. W x 2 ft. H.



