

## Unused Waukesha Model 034 Positive Displacement Pump

Mfg: Waukesha

Model: 034

Stock No: SMLR04

Serial No: 251583 99

Unused Waukesha Positive Displacement Pump. Model 34. S/N: 251583 99. Ports (2): (1) Flange of 6 3/4 in. x 1 13/16 in. opening and 12 in. x 3 1/8 in. outside dimensions, (1) 1 1/2 in. S-line clamp fittings. Flow rate for a new pump is 24 gpm at max rpm of 600. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Pump currently has single mechanical seals. Drive and pump seals can be changed to suit your application. Reliance Electric Duty Master motor: 3/1.5 hp, 1765/880 rpm, 460 V, 4.60 amps, 60 Hz, 3 phase. Dodge gearbox: Output of 350 rpm with 1750 rpm input, 5.0 ratio. Overall dimensions: 4 ft. 4 in. L x 1 ft. 3 in. W x 1 ft. 4 in. H.





