

## Wilden Diaphragm Pump

Mfg: Wilden

Model: M4

Stock No. SNBB058.4a

Serial No.

Wilden Diaphragm Pump. Model: M4. 316 stainless steel, with polypropylene center section. Inlet/outlet: 2 in. clamped s-line with Definox valve. Flow rate to 81 gpm. Max operating pressure: 125 psi. Mounted on stainless steel base. Overall dimensions: 18 in. L x 12 in. W x 21 in. H.

