

Mepaco Hydraulic Dumper

Mfg: Mepaco

Model: 519-C

Stock No. SNBB082.13

Serial No. 4595

Mepaco Hydraulic Dumper. Model: 519-C, S/N: 4595. Capacity: 1,400 lb. Carriage dimensions: 40-1/2 in. L x 28 in. W x 66 in. H. GS Hydraulic Pack, Mfr. code: 1702. Max pressure: 1,450 psi, R.V. setting: 1,450 psi, 5.3 gpm. Stauff Leeson Motor: 5 hp, 1,750 rpm, 208-230/460 V, 13.8-13 FLA, 60 Hz, 3 phase. Stauff oil filter, Model: SF-6520, 10 micron nominal. Overall dimensions: 70 in. L x 41 in. W x 92 in. H.

