

## Mokon Water Heater

Mfg: Mokon

Model: XS4A24CI

Stock No. SNBB429.3a

Serial No. 29494

Mokon Water Heater. Model: XS4A24CI, S/N: 29494. Heater: 24 KW, 30.1 amps, FLA: 34.2, Max temperature: 250 F. Inlets/outlets: (2) 1-1/2 in, (1) 1/2 in. Baldor motor: 3 hp, 3450 rpm, 208-230/460 V, 8/4 amps, 60 Hz, 3 phase. MP pump. Model: 26330, S/N: 94A1342. Inlet: 2 in.; outlet: 1-1/2 in. Capacity: 80 gpm to 60 psi. Overall dimensions: 37 in. L x 26 in. W x 43 in. H.

