

Sentinel Heat Sealer

Mfg: Sentinel

Model: 24-ASG

Stock No. SNPM013.a

Serial No. 24-610

Sentinel Heat Sealer. Model: 24-ASG. S/N: 24-610. Features (8) heat zones with temperature controllers. Power supply: 110 V, 13 amps, 60 Hz, single phase. Air line pressure (min/max): 17.5/110 psig. Jaw pressure (min/max): 10/80 psig. Belt width: 1-1/4 in. Overall dimensions: 27 in. L x 16 in. W x 27 in. H.

