

Transfer Conveyor

Mfg:

Model:

Stock No. SNPM035D.

Serial No.

Transfer Conveyor. Stainless steel. Conveyor is designed to provide multiple feeding positions. Height is adjusted by crank. Belt width: 15 in. W. Belt type (top): leather. Belt type (bottom): KVP Ram-821 (Acetal grey). Height at conveyor inlet (adjustable): 50 in. Height at conveyor outlet: 32 in. Top conveyor has a magnetic bottom. (2) Sew-Eurodrive Motors, 1/2 hp, 1700 rpm, 280/460 V, 1.85/1.07 amps, 60 Hz, 3 phase. Bonfiglioli Tipo Motor Drive (top conveyor), 14 ratio, 121 rpm (final). Bonfiglioli Tipo Motor Drive (bottom conveyor), 28 ratio, 60.71 rpm (final). Overall dimensions: 12 ft. 4 in. L x 26 in. W x 70 in. H.



