

Cherry Burrell Stainless Steel Jacketed Batch Tank - 2500 Gallons

Mfg: Cherry - Burrell

Model:

Stock No: SPGT038D.95

Serial No:

Cherry Burrell Stainless Steel Jacketed Batch Tank. Approximate capacity: 2500 gallons. 83 in. dia. x 99 in. straight wall. Tank comes equipped with upper and bottom agitators, dual spray balls and (3) Vishay – Nobel, model KIS-30KN (6744 lbs. rating) load cells. Bottom agitator dimensions (approx.) 6 ft. 2 in. L x 1 ft. W. Top agitator dimensions (approx.) 2 ft. 1 in. L x 4 in. W. Reliance electric motor: 5-2.5 hp, 1725/860 rpm, 575/575 V, 5.44/4.32 amps, 60 Hz, 3 phase. Final rpm: 48/24. Inlets / Outlets (product): (1) 4 in. diameter S-Line fitting, (1) 3 in. diameter S-Line fitting, (1) 1 ft. 6 in. diameter manhole with lid , (1) 3 in. diameter S-Line fitting. Inlets / Outlets (media): (12) 2 in. diameter S-Line fittings. Overall dimensions: 8 ft. 8 in. L x 7 ft. 5 in. W x 12 ft. 9 in. H.







