

Moyno Progressing Cavity Pump

Mfg: Moyno

Model:

Stock No. SPPF082.10

Serial No. AM21938 ZB

Moyno Progressing Cavity Pump. Type: FF6 SSE FAA, S/N: AM21938 ZB. 304 stainless steel suction housing. 316 stainless steel internal components. Nitrile rubber stator. Braided Teflon food grade packing. Suggested discharge piping lengths and/or clearance: 16 in. Minimum discharge piping lengths and/or clearance: 2 in. Baldor Industrial Motor: 3 hp, 1725 rpm, 208-230/460 V, 8.6/4.3 amps, 60 Hz, 3 phase. U.S. Motors Motor Drive: 3.60 ratio, 1750 rpm (input), 260 lb-in. torque (output). Inlets/outlets: (1) 2-1/2 in. dia. inlet, (1) 2 in. dia. outlet. Overall dimensions: 35-1/2 in. L x 41-1/2 in. W x 22 in. H.

