

Groen Steam Jacketed Kettle- 60 Gallon

Mfg: Groen

Model: H60

Stock No. SPPP595.3a

Serial No. 631 K

Groen Steam Jacketed Kettle- 60 Gallon. Stainless steel. Model: H60. S/N: 631 K. Gas-fired: natural or propane. MAWP @ 300 °F: 30 psi. Input rate: 135,000 Btuh. Electrical requirements: 115 V, 60 Hz, single phase. Open top with piston-assist lift-top lid. Features include: 180 emery grit finished interior, thermostatically controlled shut off. Inlets: (1) 3/4 in. dia. NPT (male, jacket), (1) 3/4 in. dia. NPT (male, natural gas), (1) 4 in. dia. pilot access door. Outlets: (1) 1 in. dia. NPT (female, jacket), (1) 1-1/2 in. dia. discharge, (1) 6 in. dia. exhaust port. Overall dimensions: 40 in. L x 38 in. W x 43 in. H. Overall dimensions: 46 in. L x 44 in. W x 51-1/2 in. H. Great for chain restaurants, supermarkets, schools, and healthcare facilities.

