

## 1998 Cleveland Gas Tilting Kettle- 40 Gallon

**Mfg: Cleveland**

**Model: KGL-40T**

**Stock No. SPPP621.5**

**Serial No. WT0360-98B-01**

1998 Cleveland Gas Tilting Kettle- 40 Gallon. Model: KGL-40T. S/N: WT0360-98B-01. NB: 50311. 2/3 Steam jacketed self contained stationary gas. Steam jacket permanently filled with treated, distilled water. Venting and refilling not required. Precise, consistent temperature control: less than 2 °F variance. Operating temperature range: 145 - 260 °F. Solid state controls, for temperature, low water safety, and power on/off switch. Energy efficient (65%) high performance gas-fired heating system for fast heat-up and recovery time. Horse power Input: 4.18 hp (boiler) (140,000 BTU). Natural gas, supplied with gas pressure regulator. Splash-proof front mounted pressure/vacuum gauge. Safety valve mounted toward rear of kettle. Automatic-electronic spark ignition system. Tilt mechanism on roller bearings and case hardened self-locking worm and segment gear. MAWP: 50 psi @ 298 °F, MDMT: 33 °F @ 50 psi. Electrical requirements: 120 V, 10 amps, 1 phase, 60 Hz. Jacket inlet/outlet: (2) 1 in. diameter. Tank discharge: 2 in. diameter, steam outlet: 6 in. L x 4-1/2 W. Inside dimensions: 26 in. D. x 19 in. H. Overall dimensions: 47 in. L x 41 in. W x 46 in. H.





