

Krack Stainless Steel Ammonia Evaporator- 5.8 Ton



Mfg: Krack

Model: BTR36-FIA

Stock No: SSLP052.3a

Serial No: 121230

Krack Stainless Steel Ammonia Evaporator - 5.8 Ton. Model: BTR36-FIA. S/N: 121230. Capacity: 5.8 ton. (3) Dayton motors: 1/3 hp, 1075 rpm, 115 V, 60 Hz, 4.3 amps, single phase. Fan diameter: 1 ft. 6 in. System is for quick freezing. Ammonia tank dimensions: 9 in. diameter x 1 ft. 9 in. L. MWP: 250 psi. Max. temperature: 650 deg. F. Min. temperature: -20 deg. F. Factory test pressure: 300 psi. Inlets/Outlets: (2) 1 in. port / (1) 1 1/2 in. port. Overall dimensions: 10 ft. 3 in. L x 2 ft. 5 in. W x 1 ft. 11 in. H. (BK).



Dayton
WAT TRIMMER

MODEL **3M838** HP **1/3** RPM **1075/2SPD** PH **1**
 VOLT **115** AMP **4.3** HZ **60** FRAME **48Y**
 INSUL CLASS **B** THERMALLY PROTECTED E47479
 40°C AMB AIR OVER CONT **LR47513**
 MTR. REF. NO. **KD55HXCJH9708** MFG. NO. **K85 2**

WARNING: FOLLOW ALL SAFETY INFORMATION TO REDUCE POTENTIAL ELECTRICAL SHOCK. DISCONNECT POWER BEFORE SERVICING UNIT. MOTOR MUST BE PROPERLY GROUNDED. UNUSED LEAD WIRES MUST BE INDIVIDUALLY INSULATED.

COMMON C PURPLE USE 10.0 MFD 370 V CAPACITOR
 HIGH 1 BLACK TO REVERSE ROTATION INTERCHANGE
 LOW 2 RED ORANGE AND YELLOW LEADS
 CAPACITOR BROWN REOIL EACH BEARING SAE 20 OIL
 CONTINUOUS DUTY-EVERY YEAR
 INTERMITTENT DUTY-EVERY 2 YEARS
 OCCASIONAL DUTY-EVERY 5 YEARS

DAYTON ELECTRIC MFG. CO. CHICAGO 60648, U.S.A.

Dayton
WAT TRIMMER

MODEL **3M834** HP **1/3** RPM **1075** PH **1**
 VOLT **115** AMP **4.2** HZ **60** FRAME **48Y**
 INSUL CLASS **B** THERMALLY PROTECTED E47479
 40°C AMB AIR OVER CONT **LR47513**
 MTR. REF. NO. **KD55HXCJ09704** MFG. NO. **LR4 2**

WARNING: FOLLOW ALL SAFETY INFORMATION TO REDUCE POTENTIAL ELECTRICAL SHOCK. DISCONNECT POWER BEFORE SERVICING UNIT. MOTOR MUST BE PROPERLY GROUNDED. UNUSED LEAD WIRES MUST BE INDIVIDUALLY INSULATED.

LINE 1 PURPLE USE 10.0 MFD 370 V CAPACITOR
 LINE 2 BLACK TO REVERSE ROTATION INTERCHANGE
 CAPACITOR BROWN ORANGE AND YELLOW LEADS
 REOIL EACH BEARING SAE 20 OIL
 CONTINUOUS DUTY: EVERY YEAR
 INTERMITTENT DUTY: EVERY 2 YEARS
 OCCASIONAL DUTY: EVERY 5 YEARS

DAYTON ELECTRIC MFG. CO. CHICAGO 60648, U.S.A.

PAN DUTY
MOTOR
SERIAL NUMBER
HP 1/3
HZ 60
PH 1
MFG. NO. K85 2
MTR. REF. NO. KD55HXCJH9708
THERMALLY PROTECTED
DAYTON ELECTRIC MFG. CO.
CHICAGO 60, U.S.A.

L. NICKLE & CO.
ANN ARBOR MICHIGAN U.S.A.
STAMPED WELDED INSPECTED
NAT'L
250 PSI MAX W.P.
650 PSI MAX W.P.
156 PSI MIN