

## 1998 Krones Machinery Conveyor

Mfg: Krones

Model: Glyde-Liner

Stock No. SUBF233.2a

Serial No. 994-T06

1998 Krones Machinery Conveyor. Model: Glyde-Liner. S/N: 994-T06. Uniform stainless steel design. Maximum aperture/clearance above belt: 13 in. W x 14 ft. 8 in. L. Reliance Electric Motor, 2 hp, 1750 rpm, 230/460 V, 5.8/2.9 amps, 60 Hz, 3 phase. Nord Gear Drive, ratio: 82, final rpm: 21.3. The Krones conveyor can handle glass bottles, jars, plastic containers, cans, etc. It's adjustable guide rails can adapt to a large range of heights. It's open design is optimal for debris removal. Conveyor infeed height: 41 in. Conveyor exit height: 41-1/2. Overall dimensions: 16 ft. 6 in. L x 40 in. W x 51 in. H.







