

Arrowhead Stainless Steel Table Top Transfer Conveyor

Mfg: Arrowhead Conveyor

Model: 066180-98, E-27358

Stock No. SUBF262.4a

Serial No. _____

Arrowhead Conveyor Stainless Steel Table Top Transfer Conveyor. Model: 066180-98, E-27358. Maximum product width: 3 in. Effective conveyor length: 38 in. L. Reliance Electric Motor, 1.5 hp, 1725 rpm, 208-230/460 V, 4.4-4.74/2.2 amps, 60 Hz, 3 phase. Dodge Tigear, Model: MR94668L1, 15 ratio, 115 rpm (final), 1030 in-lbs torque. Infeed and exit height: 38 in. H. Overall dimensions: 54-1/2 in. L x 24-1/2 in. W x 46-1/2 in. H.



