

Arrowhead Conveyor Corporation Bottle Conveyor

Mfg: Arrowhead Conveyor

Model:

Stock No.: SUBF290.1

Serial No.:

Arrowhead Conveyor Corporation Bottle Conveyor. Belt width: (5) 4-1/2 in. belts, (1) 7-1/2 in. belt. Maximum aperture/clearance above belt: 4-1/2 in. W x 1 ft. 1 in. H. Sew Eurodrive Motor, 1-1/2 hp, 455/2275 rpm, 230/460 V, 4.75/2.32 amps, 60 Hz, 3 phase. Sew Eurodrive Speed Reducer, ratio: 10.50, input/output rpm: 455-2275/44-215, torque: 305 in/lbs. Sew Eurodrive Motor, 3/4 hp, 1700 rpm, 230/460 V, 2.90/1.45 amps, 60 Hz, 3 phase. Sew Eurodrive Speed Reducer. Conveyor infeed/exit height: 3 ft. 5 in. Overall dimensions: 4 ft. 9-1/4 in. L x 3 ft. 4 in. W x 4 ft. 7-1/2 in. H.





