

## Beier Variator

Mfg:

Model:

Stock No. SUBF470.9

Serial No.

(9) Pump Drive, Reliance AC Motor. SM BEIER Drive, Model 15ACCY3-41, 15 hp at Max rpm, 10 hp at Min rpm, Speed Range: 0.20-0.80, 256 TC frame, type P, design B. Identification No. 1MQF20837-G8-WL, 230/460 volt, 60 Hz, 3 phase, 1,160 rpm, TEFC, 10 hp, 27/13.5 amps, 1.15 S.F. With final rpm between 145-580 rpm. Includes remote speed control option. Code G, 40 °C amb, duty cont. Pump: SM Beier Variator, Model 15ACCY3-41, Range 0.20-0.80.



# SM BEIER VARIATOR

Model Number: 15AGCYS-4/1  
Speed Range: 0.20-0.80  
Output RPM 1165  
15HP at Max RPM  
10HP at Min RPM  
Serial Number: 239879  
Reliance Motor  
Frame: 256TC  
Volts: 230/460  
Amps: 27/13.5  
Hz: 60  
Phase: 3  
RPM: 1160  
HP: 10  
Encl: TEFC





**Backside**



**Front Overview**



**Jordan Control**



**Variable Drive Gauge**



**Drive Shaft Coupling**



**Manual Control for Variable Drive**

