

Amersham Pharmacia BioProcess Engineering System 1232

Mfg: Amersham Pharmacia Biotech

Model: 44981384

Stock No: SWCS14.19a

Serial No: 1232

Amersham Pharmacia Biotech System 1232. Model: 44981384. Serial No.: 1232. Year of Manufacture: 2000. Supply Voltage: 100-230V, 50-60Hz. Largest Motor Size: 0.75 kW. Max Flowrate: 120 liters/hr. (31 gal/hr). Min Flowrate: 7.5 liters/hr. (2 gal/hr). Maximum Process Pressure: 3 bar g (~43.5 psi). Temperature Range: 4-40C (39-104F). Protection Class: IP 55. Pneumatic Supply Min/Max: 6-10 bar g (87-145 psi). Features pH meter, UV meter, flow meter, temperature readout, conductivity meter, and air detection. Weight: 338 kg (745 lbs). Utility requirements: 100-230V 50-60Hz, 6-10 bar air pressure, media feed. Wetted materials: Polypropylene, EPDM, SS316L, SS316Ti, PTFE, Glass, Quartz, Oxid Ceramic, SS904L, Titanium grade2, PEEK.







