

1996 Cetetherm Ceteplate Plate Heat Exchanger


Mfg: Cetetherm

Model: M10-BFG

Stock No: WJHM016

Serial No: 30101-40937


1996 Cetetherm Ceteplate Plate Heat Exchanger. Model: M10-BFG. S/N: 30101-40937. Number of plates: 277. Heat transfer surface area: Approx: 780 sq. ft. MAWP: 149 psi @ 275 °F. Volume: 48 gallons. Inlets/outlets: (4) 4 in. dia. ports. Overall dimensions: 6 ft. 1 in. L x 1 ft. 6-1/2 in. W x 3 ft. 2-1/2 in. H.





Alfa Laval

TYPE		MAX. WORK. PRESSURE (GAUGE)		10,3 bar
MANUF.NO.		MAX. WORK. TEMPERATURE	135 °C	°F
YEAR	VOLUME	A-873 N-277		
		316/0,5/HUIT/CLIP		



TYPE		MAX. WORK. PRESSURE (GAUGE)		10,3 bar
MANUF.NO.		MAX. WORK. TEMPERATURE	135 °C	°F
YEAR	VOLUME	A-873 N-277		
		316/0,5 BAR G 316/0		

TYPE		MAX. WORK. PRESSURE (GAUGE)		10,3 bar
MANUF.NO.		MAX. WORK. TEMPERATURE	135 °C	°F
YEAR	VOLUME	A-873 N-277		
		316/0,5/HUIT/CLIP		