

**Gaulin Homogenizer Painted Frame, Mode 3600 KF24X 1.5RS**

**Mfg: Gaulin**

**Model: 3600 KF24X 1.5RS**

**Stock No. TGP301b.30**

**Serial No. 16565580**

Gaulin Homogenizer Painted Frame. Model: 3600 KF24X 1.5RS. 2-stage manual valve assembly. 2-1/2 in. plungers. 1500 psi. Tapered seat ball valve cylinders. Maximum capacity: 3600 gph. S/N: 16565580. Overall dimensions: 72 in. L x 52 in. W x 57 in. H. Applications include viscous products like: tomato paste, orange juice concentrate. Ball valve diameter: 2 in. U.S. Motor, 15 hp, 1,725 rpm, 230/460 V, 43.3-39.2/19.6 amps, 60 Hz, 3 phase. U.S. Motor Drive, 5:1 ratio, 345 rpm (final), 4915 in-lb torque. Inlets: 1-1/2 in. dia. Q-line. Outlets: 2 in. dia. Q-line.



